



CAR RAMPS LOW ENTRY 1.5TONNE CAPACITY PER RAMP 3 TONNE CAPACITY PER PAIR

MODEL NO: **CAR3000LR**

Thank you for purchasing a Sealey product. Manufactured to a high standard, this product will, if used according to these instructions, and properly maintained, give you years of trouble free performance.

IMPORTANT: PLEASE READ THESE INSTRUCTIONS CAREFULLY. NOTE THE SAFE OPERATIONAL REQUIREMENTS, WARNINGS & CAUTIONS. USE THE PRODUCT CORRECTLY AND WITH CARE FOR THE PURPOSE FOR WHICH IT IS INTENDED. FAILURE TO DO SO MAY CAUSE DAMAGE AND/OR PERSONAL INJURY AND WILL INVALIDATE THE WARRANTY. KEEP THESE INSTRUCTIONS SAFE FOR FUTURE USE.



Refer to
instruction
manual

1. SAFETY

- ✓ Study, understand and follow all instructions before operating this device.
- ✓ Use only on a hard, level surface.
- ✓ Centre load between the sides of the ramp.
- ✓ Failure to heed these instructions may result in personal injury and/or property damage.
- ✓ No alterations shall be made to this product. Ramps are not to be used to simultaneously raise both ends or one side of the vehicle.
- ✓ Have a second person watching the ramps as the vehicle is driven on to warn of any unwanted movement.
- ✓ Be sure the wheels to be driven onto the ramps are positioned straight forward in alignment with the ramps and that the ramps are centred against the tyres.
- ✓ Ensure that the vehicle wheel rolls as far as the dished portion of the ramp.
- ✓ Never accelerate or apply brakes suddenly. Proceed slowly and cautiously. Once the vehicle reaches the top of the ramps, apply brakes to prevent over travel.
- ✓ When in place, apply the vehicle handbrake and leave in gear or in 'park' if an automatic.
- ✗ **DO NOT** exceed the rated capacity of the ramps (1500kg each, 3000kg per pair).
- ✗ **DO NOT** use this product for any purpose other than that for which it is designed.
- ✗ **DO NOT** use the ramps if they are in any way damaged.

2. INTRODUCTION

Made from durable polypropylene. These ramps are designed to allow jacking access to suitable jacking points on the vehicle. These ramps are not intended to raise a vehicle enough for under vehicle servicing.

3. SPECIFICATION

Model no:..... CAR3000LR
 Capacity each/pair: 1.5/3 tonne
 Ramp height:..... 65 mm
 Overall dimensions (L x W x H):.....700 x 200 x 80 mm

4. OPERATION

- 4.1. **Raising** (Apply section 1 safety instructions)
- 4.1.1. Push the ramp as far as possible under the tyres of the wheels to be raised.
- 4.1.2. Run the vehicle onto the ramps carefully, preferably being observed by a second person.
- 4.1.3. When the wheel sits in the dished portion of the ramp, immobilise the vehicle.
- 4.1.4. Proceed to jack the vehicle up, applying the safety details which apply to the jack.
- ▲ **CAUTION:** If working under the vehicle, ensure that it is supported by suitably rated axle stands.
- 4.2. **Lowering**
- 4.2.1. Ensure that the ramps are in place beneath the wheels before lowering the jack.
- 4.2.2. Ensure that the area beneath the vehicle is clear before lowering the jack.

ENVIRONMENT PROTECTION



Recycle unwanted materials instead of disposing of them as waste. All tools, accessories and packaging should be sorted, taken to a recycling centre and disposed of in a manner which is compatible with the environment. When the product becomes completely unserviceable and requires disposal, drain any fluids (if applicable) into approved containers and dispose of the product and fluids according to local regulations.

Note: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

Important: No Liability is accepted for incorrect use of this product.

Warranty: Guarantee is 12 months from purchase date, proof of which is required for any claim.

**Sealey Group, Kempson Way, Suffolk Business Park,
Bury St Edmunds, Suffolk. IP32 7AR**



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk